

HAMILTON-T1 Military

Configuration sheet - Software version ≥ 3.0

Configurable version = article numbers may differ from those in e-catalog

1	Ventilation unit
☐ 1610090	Ventilator ¹⁾ Hardware includes: dust and HEPA filter, and ventilation hose protective sleeve
2	Configuration sw basic
☐ 10102122	Adult/pediatric Software and consumables for adult/pediatric ventilation
☐ 10102123	Universal Software and consumables for adult/pediatric and neonatal ventilation
3	Customization
☐ 10102124	International
☐ 10102125	Japan
☐ 10102126	Canada
☐ 10102127	USA
☐ 10102128	China
☐ 10102129	Brazil
4	Handle
☐ 10102140	UniversalMount handle
5	High pressure oxygen
☐ 160470	DISS connector
☐ 160471	NIST connector
6	Communication board
☐ 10110963	CO ₂ , SpO ₂ , HAMILTON-H900 ²⁾
☐ 10110964	CO ₂ , Nurse Call, COM1
☐ 10102151	CO ₂ , SpO ₂ , COM1
☐ 10102141	Without COM board
7	NBC filter
☐ 10102132	NBC filter adapter Only with initial device order
☐ 10102133	Without NBC filter adaption option
8	Battery
☐ 10102148	Without HAMILTON-T1 battery
☐ 10102149	HAMILTON-T1 battery (1 piece)
☐ 10102150	HAMILTON-T1 battery (2 pieces)
9	Power cord
☐ 355198	US
☐ 355199	UK
☐ 355200	EU/Swiss
☐ 355308	China
☐ 10105902	Without power cord
10	Language kit
☐ 10102152	EN
☐ 10102336	EN-US
☐ 10102154	DE
☐ 10102155	ES
☐ 10102156	FR
☐ 10102157	RU
☐ 10102159	ZH
☐ 10102160	PT
☐ 10102161	IT
☐ 10108037	Without language kit
11	O₂ cell
☐ 10102146	O ₂ cell
☐ 10102147	Without O ₂ cell



HAMILTON-T1 Military with UniversalMount handle



HAMILTON-T1 Military transport case with UniversalMount handle, carrying device, breathing circuit set coaxial with flow sensor

12	Transport and accessories
☐ 10102134	Transport case
☐ 10102135	Without transport case
☐ 10102508	Transport AC cable europlug
13	Trolley and accessories
☐ 161150	Trolley
☐ 281671	Support arm, quick positioning
☐ 161152	Oxygen cylinder holder
☐ 161136	Protective sleeve (black), 170 cm
☐ 161137	Protective sleeve (black), 230 cm For ventilation hose
☐ 10101016	Small Basket
☐ 10101017	Large Basket
☐ 10101018	Height adjustable HAMILTON-H900 mount
14	Cables
☐ 161545	Cable COM1 to RS232, 26 cm
☐ 161650	Cable COM1 to RS232, 50 cm
15	Connectivity²⁾
☐ 161757	Hamilton Connect Module (Bluetooth, Wi-Fi, NFC, LAN, HL7)
☐ 161759	Ethernet (LAN, HL7)
16	Gas supply
☐ 279947	Gas source switch Requires PN 279952, PN 279953, PN 279954
☐ 279952	O ₂ hose switch to ventilator, NIST
☐ 279953	O ₂ hose switch to oxygen cylinder, DIN
☐ 279954	O ₂ hose switch to gas socket, DIN
☐ 279949	Pressure reducer valve
☐ 161590	NIST connector 90° for PN 160471
☐ 161591	DISS connector 90° for PN 160470
17	DC connectors and cables
☐ 161595	DC connector box set
☐ 161596	DC connector set
☐ 161622	DC input cable open, metal
☐ 161623	Car cable, metal
☐ 161624	DC input cable, metal
18	Batteries and charger
☐ 369108	Li-Ion battery, hot-swappable
☐ 369104	Desktop smart battery charger and calibrator Requires country-specific power cord
19	Extended warranty
☐ 700603	1 year
☐ 700604	2 years
☐ 700605	3 years
20	Cuff pressure control²⁾
☐ 951001	IntelliCuff pressure controller

1-11 Required parts (choose at least one of each group)

12-20 Optional parts

1) Special terms and conditions apply

2) For an additional COM1 interface the Y-Cable PN 10077038 is required

3) Not available in all markets

21	HAMILTON-H900
☐	950001 HAMILTON-H900, 220-240V ¹⁾
☐	950004 HAMILTON-H900, 110-127V ¹⁾
☐	950008 HAMILTON-H900, 100V ¹⁾
22	Mounting solutions
A	Compatible with all handles
☐	161439 Shelf mount plate
☐	161449 Shelf mount system
☐	161198 Shelf mount system plate
☐	161199 Shelf mount system shelf
	Not for Fold away handle:
☐	161920 Shelf mount plate with spacers
☐	161430 Wall mount plate for carrying device
☐	161144 Rail adapter set for wall mount Requires PN 161430
B	For UniversalMount handle only
☐	161146 Rugged rail mount adapter
☐	161145 Pole mount adapter
☐	161395 Ceiling mount rail
23	SpO2 and CO2 measurement
☐	282157 CAPNOSTAT®-5 CO2 sensor Requires communication board and mainstream airway adapter
☐	281928 LoFlo sidestream CO2 sensor Requires communication board and sidestream CO2 airway adapter
☐	282010 SpO2 sensor adapter (Nihon Kohden) ¹⁾
☐	282009 SpO2 sensor adapter (Nihon Kohden) ²⁾
☐	10109010BA Masimo RD SET adapter kit - basic
☐	10109010 Masimo RD SET adapter kit - configurable

24	Software license keys
☐	161064 DuoPAP/APRV
☐	161065 Trends/Loops
☐	161066 NIV/NIV-ST
☐	161078 Neo/Ped function for 200g to 30 kg ³⁾
☐	161079 nCPAP option for neonates Requires PN 161078 or PN 10102123
☐	161088 High flow oxygen therapy ¹⁾
☐	161090 NVG-Night Vision Goggle option
☐	161092 Speaking valve ¹⁾
25	INTELLiVENT®-ASV® 1,4)
C	Kits (incl. software license key and accessories)
☐	10102042 INTELLiVENT-ASV Nihon Kohden
☐	10102043 INTELLiVENT-ASV Masimo
D	Software license key
☐	161098 INTELLiVENT-ASV

21-23 Optional parts

24-25 Software options

A-B Mounting solutions

C-D Variations

1) Not available in all markets

2) Only for USA/Canada

3) For new devices order PN 10102123 instead

4) Order your INTELLiVENT-ASV manual separately

Accessories and consumables

Specially developed for the highest possible patient safety and ease of use, Hamilton Medical Originals ensure the best performance and safety of your Hamilton Medical ventilator. Furthermore, we offer the full product range of accessories and consumables for mechanical ventilation - for neonates, pediatrics and adults. Choose between reusable and disposable parts, according to your institutional policies.

For the full product portfolio and detailed information about included parts, see www.hamilton-medical.com/e-catalog

